






SERPAC **RB66X06Y28Y**
Electronic Enclosures




BOTTOM VIEW



SECTION B-B



SIDE VIEW



SECTION A-A

—PN-RB66X28Y

ALL DIMENSIONS ARE $\pm .010"$

5/8/2023

2009 Wright Ave., La Verne, Ca. 91750

Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com

RB66X06C28C 
(Part shown, no material (X) specified)

PN	Description
RB66-X06Y	(1) RB66-X06Y Top
RB66X28Y	(1) RB66X28Y Bottom
8066	(1) RB66 O-Ring
6051	(4) #6-32 X 1" Captive PH Pan Hd Screw
6022	(4) #10 High/Low Pan Hd x 1/4"
6113	(4) #6-32 Threaded Insert

 =INTERIOR DIMENSIONS (@ BOTTOM)

2 =STANDARD COLORS (Y) ARE: BLACK (B), CLEAR (C) AND GRAY (G)
TOPS AND BOTTOMS ALL POSSIBLE COMBINATIONS AVAILABLE
STANDARD MATERIALS (X) IS: POLYCARBONATE (P)


- Watertight enclosure meets or exceed Nema 4 and or IP67.

DIMENSIONS in Inch
[mm]

SERPAC

Electronic Enclosures

RB66 Circuit Board (Fits all Parts starting with RB66)



(REFERENCE ONLY)