











Max. Temperature: 260°C during 10 seconds.  
Find further technical information on DS 09550200302

|                   |    |          |                   |                                 |
|-------------------|----|----------|-------------------|---------------------------------|
| 0955 129 6812 333 | 2  | 4-40 UNC | Black insulator   | Samples                         |
| 0955 129 3811 741 | 1  | M3       | Black insulator   | Reel packing:<br>140 connectors |
| 0955 129 3812 741 | 1  | 4-40 UNC |                   |                                 |
| 0955 129 6811 741 | 2  | M3       |                   |                                 |
| 0955 129 6812 741 | 2  | 4-40 UNC |                   |                                 |
| 0955 129 7811 741 | 3  | M3       |                   |                                 |
| 0955 129 7812 741 | 3  | 4-40 UNC |                   |                                 |
| Part number       | PL | Nut      | Index designation |                                 |

|                                                                                       |  |                                                                |                       |                       |                |                      |                             |                    |                                                          |             |
|---------------------------------------------------------------------------------------|--|----------------------------------------------------------------|-----------------------|-----------------------|----------------|----------------------|-----------------------------|--------------------|----------------------------------------------------------|-------------|
|  |  | All Dimensions in mm<br>Original Size DIN A3                   |                       | Scale<br>2:1          | Free size tol. |                      | Ref.                        |                    |                                                          |             |
|                                                                                       |  |                                                                |                       |                       |                |                      | Sub.                        |                    |                                                          |             |
|  |  | All rights reserved                                            |                       | Created by<br>ZHUANGJ |                | Inspected by<br>LUOK | Standardisation<br>HOFFMANN | Date<br>2018-11-29 | State<br>Final Release                                   |             |
| Department EL PD                                                                      |  | Title<br>D-Sub str SMT 9-pole male ass with nut and ground pad |                       |                       |                |                      |                             |                    | Doc-Key / ECM-Nr.<br>100236622/UGD/001/C<br>500000139800 |             |
| HARTING Electronics GmbH<br>D-32339 Espelkamp                                         |  | Type<br>TB                                                     | Number<br>0955129X81X |                       |                |                      |                             |                    | Rev.<br>C                                                | Page<br>1/1 |