



Part Number : [1301050056](#)
Product Description : Watertite Wet Location Incandescent Hand Lamp, 100W for use with Low Voltage Workstation with Screw Release TEFLON Guard, Cord Type 14/2 SOOW, 15.24m (50.0') Cord Length
Series Number : 130105
Status : Active
Product Category : Lamps and Lights
Engineering Number : 1646-12



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130105
Description	Watertite Wet Location Incandescent Hand Lamp, 100W for use with Low Voltage Workstation with Screw Release TEFLON Guard, Cord Type 14/2 SOOW, 15.24m (50.0') Cord Length
NEMA Configuration	Non-NEMA
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps, Specialty Light
UPC	78678862526

Agency

CSA	E59049
UL	E59049

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	12V AC/DC

Physical

Bulb Type	Incandescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	14/2 SOOW
Depth	120.65mm (4.750")
Duty	Wet Location

Guard Included	Yes
Guard Type	Screw Release
Height	457.20mm (18.000")
Lamp Type	A21
Length	N/A
Material - Globe	Teflon*
Material - Guard	N/A
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Sep 18, 2025