

CATALOG LISTING
BZE6-7RN18
PAGE 1 OF 1
RELEASE NO. PR-22651
REPLACES

ISSUE
2

REVISIONS



DDM/CAD
DRAWN

JAK
20 FEB 97

CHECK
23NOV05

BP

CHECK



NOTE

1 - 3X 6-32 UNC X (.219) TERMINAL SCREW AND CUPWASHER

2 - SEAL RATING: NEMA1,3
IP54

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION
CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ——— 7 OZ MAX	CONTACT ARRANGEMENT	DO NOT SCALE PRINT
OPERATING POSITION ——— 15° MAX	S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
SWITCH BASIC REPLACEMENT——BZ-7R-A2	L96	ONE PLACE (.0) ± .030
	15A 125, 250 OR 480 VAC	TWO PLACE (.00) ± .015
	1/8HP 125 VAC, 1/4HP 250 VAC	THREE PLACE (.000) ± .005
	1/2A 125 VDC, 1/4A 250 VDC	ANGLES ±
	CE 1.5A, 240Vac	WEIGHT

ANSI Y14.5M-1982 APPLIES