





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/26/18	
A		ADDED LAYOUT	3/16/20	OW/KC
B		UPDATED DRAWING	11/25/22	JJ/HC
C		UPDATED DRAWING	12/13/22	LH/HC



SPECIFICATIONS:

Material:
 Housing: PA46, Color: Black
 Contact: Brass, 5u" Gold plated over Nickel
 Magnet: N52
 Electrical:
 Voltage rating (Per Contact): 12 Volts
 Current rating (Per Contact): 2 A max
 Contact resistance: 50 mohms max
 Temperature Rating:
 Operating temperature: -40°C to $+85^{\circ}\text{C}$
 Environmental:
 Lead free, RoHS compliant.



Mating with: PH1-C1853-04-MVP-7365

Mating with: PH1-C1854-04-MVP-7467

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED			<div>ADAM TECH</div> <div>909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710</div>		
MM		ANGLE			
.X	± .20	.X			± 2°
.XX	± .15	.XX			± 0.5°
.XXX		± .10			
DRAWN		AY	7/26/18		
CHECKED		CK	7/26/18		
APPROVED					
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH					

TITLE			1.80MM PITCH POGO PIN HEADER, FEMALE, 4P, SINGLE ROW, STRAIGHT		
SIZE		PART NO.			REV
X		PH1-C1846-04-FVP-66			C
REF:		S00185C		SCALE:	NTS
				SHEET	1 OF 1