



**Part Number :** [2130694800](#)

**Product Description :** FA2 Mechanical Feed Crimp Applicator for DuraClik Robust Crimp Terminals, 0.30mm<sup>2</sup> and 0.50mm<sup>2</sup> AVSS Wire

**Series Number :** 207127

**Status :** Active

**Product Category :** Applicators and Crimp Modules



---

## Documents and Resources

### Tooling Specifications

[2130694800-000.pdf](#)

[TM-638000029-001.pdf](#)

[638080200-000.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FA2 Mechanical Feed Crimp Applicator for DuraClik Robust Crimp Terminals, 0.30mm <sup>2</sup> and 0.50mm <sup>2</sup> AVSS Wire
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FA2,DuraClik
Tool Type	Applicator
UPC	195842830103
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

## Physical

Net Weight	4672.002/g
------------	------------

---

## Applicable Parts

Description	Part Number
DuraClik Robust Wire-to-Board Crimp Receptacle Terminal, Female, AVSS/AESSX 0.30mm <sup>2</sup> and 0.50mm <sup>2</sup> Wire, Tin (Sn) Plating	<u>5031160102</u>

---

This document was generated on Dec 26, 2025