



Part Number : [1300940232](#)
Product Description : Standard Duty Support Grip,
Single Eye, Closed Mesh, Single Weave, Cable
Diameter 15.88-19.05mm (.625-.750"), Approximate
Break Strength 435.45kg (960 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Number : 35031



Documents & Resources

Drawings

[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Single Eye, Closed Mesh, Single Weave, Cable Diameter 15.88-19.05mm (.625-.750"), Approximate Break Strength 435.45kg (960 lbs)
Product Name	Standard Duty
Type	Support Grip
UPC	78678835031

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	435.45kg (960 lbs)
Bale Length	0.203m (8.00")
Body Style	Straight
Cable Diameter	15.88-19.05mm (.625-.750")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.279m (11.00")
Net Weight	587.000/g
Number of Holes	N/A

O-Ring	N/A
Thread Size	N/A

This document was generated on Sep 13, 2025