



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

69-ELBP-2 Battery Power Supply for EL Wire



Description:

The 69-ELBP-2 uses 2 (1.5VDC) AA batteries to drive up to a 3 meter (9.8 foot) max length of EL Wire.

Features:

- Modes – On / Flash / Fast-Flash / Off

Specifications: (@ +12°C, 2 AA Batteries, 3VDC)

- DC Input: 3VDC
- Output Power: 1.0W
- Frequency: 2000 – 2200Hz
- Output (RMS): 135–145VAC
- Optimal Load Length: 3 meters (9.8 feet)
- Operating Temperature: +14° to +122°F (–10° to +50°C)
- Storage Temperature: –22° to +140°F (–30° to +60°C)
- Size: 3.583" (91mm) x 1.30" (33mm) x 0.709" (18mm)
- Weight: 1.41oz. (0.04kg)