


REV.	DATE	DESCRIPTION
NC	12/23/97	INITIAL RELEASE
A	02/21/07	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex				
8						DRAWN	G.R.S.					02/21/07
7						CHECKED			PART DESCRIPTION SMA FOUR (4) HOLE PANEL RECEPTACLE JACK (.500” SQ. MOUNT HOLES)			
6						ISSUED						
5						SHEET	1 OF 1		PART NO. 132215			
4	CONTACT PIN	BER. COPPER	GOLD	1	CAD FILE			DWG. NO. 132215.DWG				
3	INSULATOR (B)	TEFLON	NATURAL	1	C:/132/132215.DWG							
2	INSULATOR (A)	TEFLON	NATURAL	1	DO NOT SCALE DRAWING							
1	BODY	BRASS	GOLD	1								
	DESCRIPTION	MATERIAL	FINISH	QTY								