

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=10134358-002LF* > 10134358-002LF

10134358-002LF

10134358-002LF : Two stage Screwless Terminal Block XDV 2,5 vertical blue



ACTIVE

RoHS Compliant

Distributor Stock

 [Print Datasheet](#)

FCI Brings You More

 > [Contact our sales/technical support](#)

 > [Sample request](#)

 Customer drawing

 Environmental Compliance Report

Specifications

Download document

General	Dimensional	Electrical	Physical	Approvals / Certifications	Mounting
General					
Pollution Degree	3				
Insulating Material Group	I				
Number of contacts (Total)	2				
Number of decks	Double				
Packaging	Pack				
Product Type	Pluggable Terminal Blocks				
Attachment type (Board)	DIN Rail				
Dimensional					
Width	5 mm				
Conductor cross section solid (min-max)	0,5 / 2,5 sqmm				
Conductor cross section stranded (min-max)	0,5 / 2,5 sqmm				
Length (Overall)	77 mm				
Strip length (Wire)	max 8 mm				
Solid wire size (AWG)	24-12				
Height (Total)	52 mm				
Electrical					
Nominal Current	12 A				
Nominal Voltage	400 V				
Rated Surge Voltage	8kV				
Surge Voltage Category	III				
Current Rating (Max)	12 A				
Physical					
Color (Housing)	Blue				
Flammability rating	UL 94 V-2				
Material (Insulator)	PA				
Approvals / Certifications					
Approvals / Certifications	cURus				
Mounting					
Mounting style	Omega TH 35				

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.

Downloaded from [Arrow.com](#)