



Part Number : 1301030060

Product Description : Watertite Wet Location
Incandescent Hand Lamp Only, 100W with
Ungrounded Cast Aluminum Reflector Guard

Series Number : 130103

Status : Active

Product Category : Lamps and Lights

Engineering Number : 1207R



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights

Series	130103
Description	Watertite Wet Location Incandescent Hand Lamp Only, 100W with Ungrounded Cast Aluminum Reflector Guard
NEMA Configuration	N/A
NEMA Rating	NEMA 4X
Product Family	Hand Lamps
Product Name	Watertite
Type	Hand Lamps
UPC	78678861305

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Reflector, Screw Release
Height	457.20mm (18.000")
Lamp Type	A21
Length	N/A
Material - Globe	Tempered Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Outlet	None

Packaging Type	Carton
----------------	--------

This document was generated on Dec 16, 2023