

ENCLOSURE HARDWARE ▾

LED INDICATORS ▾

LIGHT PIPE SELECTOR

LED MOUNTS, HOLDERS

LEDs

LIGHT PIPES

BOARD MOUNT LED ASSEMBLIES

PANEL MOUNT LED ASSEMBLIES

LED LIGHTING ▾

SOLUTIONS

RESOURCES ▾

R2D-6.0-WHT



ORCAdapt Flexible Light Pipe System, 2mm. Fiber Optic Core, 4.2mm. Base Dia. Dome Lens, 6.0in. Length, Rectangular White LED



Datasheet



3D Model



Request Samples



RoHS Docs

FEATURES

VALUE ADDED

CHECK STOCK

- High Intensity LED, 8000mcd, Color Emitted: White
- 4.2mm. Base Diameter Dome Lens Cap
- Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info
- Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear
- Rear Panel Mount Lens



Enclosure Hardware
LED Indicators
LED Lighting

New Products
Locate a Distributor / Sales REP
Quality Assurance / RoHS

Product Info Center
Terms & Conditions
My Bivar



100%
Employee
Owned