Part Number : 191310038
Product Description : InsulKrimp Block Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Length 19.94mm, Carton
Series Number : 19131
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : AA-234-06X



Documents and Resources

Drawings

191310038_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-009-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19131
Description	InsulKrimp Block Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Length 19.94mm, Carton
Keyword	Spade Terminal, Spade Terminals
Product Name	InsulKrimp
Style	Spade Block
Type	Spade Connector, Metric Spade Connector
UPC	800753101616

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Color - Resin	Natural

Downloaded from Arrow.com.

Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.617/g
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	5-6 (M3-3.5)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.70mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm^2	0.35-0.80

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm^2 (Rings, Spades, Hooks, Block Spades and Flanged Spades)	640010100
PremiumGrade Hand Crimp Tool for Insulkrimp Terminals and Splices, 22-10 AWG (Rings, Spades, Hooks, Block Spades and Flanged Spades)	640010300
Crimp Head for the AT-200 Pneumatic Hand Tool	640050100
Crimp Head for the AT-200 Pneumatic Hand Tool	640050300
ServiceGrade Hand Crimp Tool for Field Repair only, for	640160036

Downloaded from Arrow.com.

production use our PremiumGrade Tool	

Downloaded from Arrow.com.