



Part Number : [2245722115](#)
Product Description : Pre-Crimped Lead Stac64-Female-to-Pigtail, Tin (Sn) Plating, 450.00mm Length, 0.50mm² Wire, Black
Series Number : 224572
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[2245722115 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	224572
Description	Pre-Crimped Lead Stac64-Female-to-Pigtail, Tin (Sn) Plating, 450.00mm Length, 0.50mm ² Wire, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Stac64 Crimp Terminals
Product Name	Stac64
UPC	196823398315

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	14V DC

Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3.173/g
Number of Rows	1
Packaging Type	Bag

Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	FLRYW125-B
Wire Size mm ²	0.50

This document was generated on Oct 05, 2025