Specifications



Photo is representative





Eaton DRA73-101-R

Eaton DRA inductor, 102 uH, 0.682 A Irms, 0.763 A ISAT, 710 mΩ resistance, SMT mounting, Ferrite, 2-pins, 1350 qty.

General specifications	
PRODUCT NAME	Eaton DRA inductor
CATALOG NUMBER	DRA73-101-R
UPC	051712827928
PRODUCT LENGTH/DEPTH	7.6 mm
PRODUCT HEIGHT	3.55 mm
PRODUCT WIDTH	7.6 mm
PRODUCT WEIGHT	0.64 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.682 A
ISAT	0.763 A
PACKAGE QUANTITY	1350
MATERIAL	Ferrite
AUTOMOTIVE GRADE	Yes
CONTACT CONFIGURATION	Two-pads
TEMPERATURE RATING	-40 to 165 °C
RESISTANCE	710 mΩ
SIZE	7.5x7.5x3.4
TERMINALS	2 Pads
SERIES	DRA73

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - DRA73-101-R Eaton DRA automotive shielded drum core power inductors data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.