



Part Number : [1300980043](#)

Product Description : MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, Straight Male with O-Ring, Cable Diameter 3.18-4.75mm (.125-.187")

Series Number : 130098

Status : Active

Product Category : Cable Grips

Engineering Number : 5520W



Documents & Resources

Drawings

[1300980043_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, Straight Male with O-Ring, Cable Diameter 3.18-4.75mm (.125-.187")
NEMA Rating	NEMA 6P
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678855202

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	3.18-4.75mm (.125-.187")
Color - Grommet	Yellow
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
O-Ring	Yes
Thread Size	1/2" NPT

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	<u>1300990143</u>
MAX-LOC O-Ring, 1/2" NPT	<u>1301800314</u>

This document was generated on Jan 11, 2025