



Search for any Microchip or Competitor Part Number

 \$0.00[Products](#)[Request Large-Quantity Pricing](#)[Design Services](#)[Purchasing Tools](#)[Support](#)[888-624-7435](#)[Home](#) / [Development Tools](#)

EV8810A High-Speed 10/100/1000 Ethernet Transceiver Customer Evaluation Board

The EV8810Ai is a PHY Evaluation Board EVB that interfaces a MAC controller to the single chip LAN8810Ai Ethernet PHY. The LAN8810Ai is compliant with IEEE 802.3ab 1000BASE-T, IEEE 802.3u Fast Ethernet, and ISO 802-3/IEEE 802.3 10BASE-T standards. The device comes in a 72 pin QFN, lead-free RoHS compliant package with flexibe configuration for LED status indicators. Also implements reduced power operating modes.

End of Life

This product is no longer available to purchase, please contact us for more information.

Contact Us

[Contact Us For More Information](#)

Would you like to have more flexibility for your orders?

Apply for a Microchip Business Account and have access to unique features.

- ✓ Request a quote for your large-quantity needs
- ✓ Schedule your orders, up to 3 years in advance
- ✓ Buy now, pay later with a Microchip credit limit

[Apply for a Business Account](#)[BACK TO TOP](#)[Accessibility Menu](#)

Search for any Microchip or Competitor Part Number

 \$0.00

[Get Help with Your Project](#)

[International Shipping Information](#)

[Return Policy](#)

[Terms and Conditions](#)

[Privacy Notice](#)

[Your Privacy Choices](#) 

[Frequently Asked Questions](#)

[Accessibility Menu](#)

[Create a New Account](#)

[Apply for a Business Account](#)

[About Us](#)

[Cross Reference Tool](#)

[Conflict Minerals](#)

[Export Control Data](#)

[RoHS Information](#)

[Technical Product Support](#)

[Find an Authorized Design Partner](#)

We'd love to hear what you think

[Give us feedback](#)

Customer Service Phone Numbers

Australia 1 800 193 884	Austria 0 800 298 364	Belgium 0 800 78 586	Bulgaria 00800 210 0073	Canada 1 888 624 7435	China 400 820 5079
Croatia 0800 890 094	Czech Republic +420 800 012 055	Denmark 802 53233	Estonia / Lithuania / Latvia 8 800 3 31 17	Finland 0 800 917 739	France 0 800 900 990
Germany 0 800 180 0121	Greece +30 800 848 1206	China - Hong Kong SAR 400 820 5079	Hungary 06 801 099 86	Iceland +45 4450 2827	India 000 800 1009 343
Ireland 1 800 901 628	Israel 1 80 945 0151	Italy 800 786 648	Japan +632 8479 2850	Latin America 1 888 624 7435	Moldavia 0 800 61527
Netherlands 0 800 022 4021	New Zealand 0 800 480 421	Norway 800 690 17	Philippines 180011102092	Poland 00 800 112 47 69	Portugal 800 819 068
Romania 0 800 896 371	Russia 8 800 301 7156	Slovakia 0 800 606 095	Slovenia 0 800 81772	South Africa 0 800 981 024	South Korea 0 82 2 554 7200
Spain 900 808 071	Sweden 0200 99 0585	Switzerland 0 800 848 253	Taiwan 00 801 127 676	Turkey 00 800 1420 30262	United Kingdom 800 032 3850
United States 1 888 624 7435	ASEAN countries not listed +632 8479 2850	European countries not listed +44 20 4602 9229			

