



HN-214DX

Order Number HN-214DX

Compact Outdoor 2.4GHz Wireless Serial Modem with DIN-rail mount serial interface and four foot cable and external antenna connector

- 2.4GHz Proprietary FHSS Serial Modem
- Network Topology: Point-to-Point and Point-to-Multipoint

460.8 Kbps RF data rate

- Outdoor NEMA 4X/IP 66 enclosure
- Compatible with HN 10 Series Products
- Ideal for pole mounting

Recommended

In Production

?

[Data Sheet](#)

[Contact Us](#)

[Add to Compare List](#)



Description

Specs

Documents

Applications

Purchase

Minimum Order Quantity	1
Product Type	Serial Modem
Frequency	2.4GHz
Antenna	Reverse TNC
RF Conn/ Antenna	Reverse TNC
Operating Temperature Range	-30 to +70
Operating Temperature °C (min)	-30
Operating Temperature °C (max)	70
Mounting Type	DIN-rail
Dimension	130.00 x 79.00 x 35.00 mm
Supply Voltage min	9.0
Supply Voltage max	30.0
Transmit Power Configurable	Yes
Transmit Power	100mW
Receiver Sensitivity	-93 dBm
Data Rate	460.80 kbps
Data Rate Configurable	No
Range	Indoor 100m, Outdoor 10,000m
Technology	Proprietary FHSS
Network	Point-to-Point and Point-to-Multipoint
Host Interface	RS-232C
FCC/IC Certified	FCC/IC Certified
ETSI Certified	ETSI Certified
RoHs Compliant	Yes
CE Compliant	CE Marked
ISO9001	Yes

Related Links

- [Applications for Wireless](#)
- [Support for Wireless](#)
- [Wireless Modules for IoT Applications](#)
- [Wi-Fi/Bluetooth Modules for NXP i.MX](#)
- [LoRa Modules](#)

Related Product Categories

- [« Go Back](#)
- [Wi-Fi](#)
- [Wi-Fi + Bluetooth](#)
- [Bluetooth](#)
- [LPWA Modules](#)
- [IoT System-On-Module **New*](#)
- [802.15.4](#)
- [Wi-Fi Bluetooth for NXP i.MX](#)
- [HyperMesh / FHSS](#)
- [M2M & Sensor Networking](#)
- [Wireless Network / Telemetry](#)
- [RFIC Radios](#)
- [Resonators](#)
- [Filters](#)

