

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDERICK, MINNESOTA

FED. MFR CODE 91929

SWITCH - BASIC

CATALOG LISTING

BA-2RV241-A2

ABS3000

JG18906

BA-2RV241-A2

PAGE 1 OF 1

M

DRAWING
NUMBER


10

ISSUE


RELEASE NO. PR - 4426 REPLACES
CMH 04 SEP 09
CHECK
PSR 29 MAY 07
CHECK
PSR 16 JULY 62
CHECK
DAW 10 MAY 62
CHECK
MBF 10 MAY 62
CHECK

REVISIONS

A	CO 16804	10 MAY 62
B	TR 4426	7 SEP 74
C	CO 73287-J	22 NOV 93
D	CO 77588	29 MAR 94
E	CO 93346	26 AUG 98
F	18687	20 FEB 06
G	0030970	29 MAY 07
H	0056248	04 SEP 09



3X 6-32 UNC X (.219)
BINDING HEAD COMBINATION
TERMINAL SCREW AND
CUPWASHER



NOTE -

① - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON
1.000 ± .002 CENTERS

2 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE--- 2 1/2 OZ MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE----- 1/2 OZ MIN		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
PRETRAVEL----- .625 MAX	20A-125, 250 OR 480 VAC, 10A-125 VAC "L" 1HP-125 VAC, 2HP-250 VAC CODE L23 B 1/2A-125 VDC, 1/4A-250 VDC L288 L315 L308	TOLERANCES ARE: ONE PLACE (0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
DIFFERENTIAL TRAVEL----.109 MAX	20(3)A 250V ~ T85 SE4	WEIGHT
OVERTRAVEL----- .078 MIN		

RASTER

DRAWN

5-90378