Part Number : 1301470145
Product Description : Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 2 Pole/3 Wire, NEMA L7-20 277V
Series Number : 130147
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 67W49



Documents and Resources

Drawings

1301470145_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 2 Pole/3 Wire, NEMA L7-20 277V
IP Rating	IP67
NEMA Configuration	NEMA L7-20
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871561

Agency

CSA	LR6837
UL	E68122

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	277V

Physical

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female

Downloaded from Arrow.com.

Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	2-pole/3-wire
Receptacle Type	Single

Downloaded from Arrow.com.