


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00574	Connector, USB A 2.0 Plug, molding style, 180°, nickel plated shell, black insulator	2	
2	30-01272	Wire, 4C, 1PR + 2C, 28 AWG, UL2725, 30V, 80C, 4.1 mm, shielded, VW-1, PVC, 79A, USB 2.0, nylon braid	1	
3	24-00210	Overmold, plug, USB A, slim design for aluminum shell	2	PVC, black
4	55-00073	USB A plug aluminum shell, 13x13.5x5.9 mm	2	black



Notes:
Functionally equivalent components may be substituted

Wiring diagram		
50-00574	Wire Color	50-00574
1	Red	1
2	White	2
3	Green	3
4	Black	4
Shell	Drain & Shield	Shell

Revision:	Date:	Description:	Prepared:	Notes:	TENSILITY tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com		
A	08/12/2019	Initial Release	Verified:				
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Description:	Size:	Part number:	
				Cable, 1000 mm, 50-00574 USB A plug to same, 28 AWG, nylon braided	A	10-03380	
					Scale: 1:1	 	Sheet 1 of 1