

 [Live Product Chat](#)



CI 2- Housings and Contacts

 [Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

- Contact
- Contact Diameter = 1.60 mm
- Contact Type = Pin
- Packaging Method = Strip
- Wire Range = 1.00-2.50² [17-13.5]
mm [AWG]

[View all Features](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#)

Product Drawings: • CI 2 Kontaktstift (PDF, English) Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: (CAD Format & Compression Information) • 2D Drawing (DXF, Version C2) • 3D Model (IGES, Version C2) • 3D Model (STEP, Version C2) List all Documents	Additional Information: • Product Line Information Related Products: • Tooling
--	--

Product Type Features: • Product Type = Contact • Material = Brass • Insulation Diameter (mm [in]) = 2.20-3.00 [.086-.118] • Connector Line = CI 2 • Mount = Wire Crimp • Comment = Regarding the Econoseal E program only FLR-wires are allowed when using 2.5mm² wires, the insulation dia. may not exceed 3.0mm Electrical Characteristics: • High Current = No Termination Related Features: • Solder Tail Contact Plating = Pre-Tin Body Related Features: • Contact Diameter (mm [in]) = 1.60 [0.063] • Wire Range (mm [AWG]) = 1.00-2.50² [17-13.5] • Insulation Type = FLR	Contact Related Features: • Contact Type = Pin Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant Packaging Related Features: • Packaging Method = Strip • Packaging Quantity = 4,000 Other: • Brand = AMP
---	--