
PRODUCT NO.	ITEM	PART NAME	Q'TY	MATERIAL	PLATING
114B-40B00-R02	1	BODY	1	LCP	
	3	CONTACT	124	PHOSPHOR BRONZE	GOLD 3u"
	4	LATCH	2	STAINLESS	



Plastic Body : LCP, Color Black.
Contact: Phosphor Bronze Alloy (C5191R-H)
Contact area: Gold 3 micro inches
⚠6 Solder area: Gold flash
All under-plated Ductile Nickel 50 micro inches (Min.)
Latch :SUS304R-1/2H, Matte Tin Plated
Contact Resistance: 30 mΩ (Max)
Insulation Resistance: 500 MΩ (Max.)
Dielectric Withstanding Voltage:
Mate connectors; apply 250V AC at 60 Hz(rms.)
Contact Normal Force: 50 gf per pin (Min.)
soldering heat: 260℃
Rating Voltage: 25V AC
Rating Current: 0.3A(Max.)/(1PIN)
Operating Temperature: -40℃ to +90℃
Storage Temperature: -40℃ to +90℃

114B-40 B 0 0-R02
1 2 3 4

1.Stand off
s/o:4.0mm

2.Contact Plating
B:3u" Gold Plating

3.Color
0:Black

4.RoHS


REV.	DESCRIPTION	DATE	REV.	DESCRIPTION	DATE
⚠6	ECR2100009	2021/03/30			

UNLESS OTHERWISE SPECIFIED TOLERANCE

ANGLES	ANG.	±5°
LINEAR	0.	±0.3
	0.0	±0.25
	0.00	±0.20
SCALE	AS SHOWED	UNIT: mm
DRAWN	Willis	2012/08/03
CHECKED	Angel	2012/08/03
APPROVED	Ken	2012/08/03

ATTEND
www.attend.com.tw
DRAWN NAME: Mini PCI Socket H:4.0,Metal Grounding Type
PRODUCT NO. 114B-40B00-R02
FILE NAME 114B-40B00-R02_B_6
SIZE A4 REV. 1.0

Downloaded from Arrow.com.



RECOMMENT PC BOARD LAYOUT

REV.	DESCRIPTION	DATE	REV.	DESCRIPTION	DATE
6	ECR2100009	2021/03/30			

UNLESS OTHERWISE SPECIFIED TOLERANCE

ANGLES	ANG.	±5°
LINEAR	0.	±0.3
	0.0	±0.25
	0.00	±0.20
SCALE	AS SHOWED	UNIT: mm
DRAWN	Willis	2012/08/03
CHECKED	Angel	2012/08/03
APPROVED	Ken	2012/08/03

ATTEND


www.attend.com.tw

DRAWN NAME: Mini PCI Socket H:4.0,Metal Grounding Type

PRODUCT NO.	114B-40B00-R02
FILE NAME	114B-40B00-R02_B_6

SIZE A4 REV. 1.0

Downloaded from Arrow.com.



NOTES:

1. PACKING STYLE 20 PCS/TRAY
   300 PCS/INNER CARTON
   1200 PCS/OUTER CARTON
2. MATERIAL TRAY:PET

NO.	PACKING NAME	PACKING QTY: PCS/T	PACKING QTY: T/CTN.	UNIT	NOTE
7	LABEL	1		PCS	
6	LABEL	4		PCS	
5	PE BAG	1		PCS	
4	DRYER	4		BAG	
3	OUTER CARTON	1		PCS	
2	INNER CARTON	4		PCS	
1	TRAY	20	64+4 1200	PCS	

REV.	DESCRIPTION	DATE	REV.	DESCRIPTION	DATE

UNLESS OTHERWISE SPECIFIED TOLERANCE

ANGLES	ANG.	±5°
LINEAR	0.	±0.3
	0.0	±0.25
	0.00	±0.20
SCALE	AS SHOWED	UNIT: mm
DRAWN	Willis	2012/08/03
CHECKED	Angel	2012/08/03
APPROVED	Ken	2012/08/03

ATTEND
www.attend.com.tw

DRAWN NAME: Mini PCI Socket H:4.0,Metal Grounding Type

PRODUCT NO.	114B-40B00-R02
FILE NAME	114B-40B00-R02_D_3

SIZE A4 REV. 1.0

Downloaded from Arrow.com.