

Honeywell Sensing and Control

Search



3455RCG 82700025
Thermostats
 (Home : Products)

narrow your search

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1702)
- Sensors (6223)
- Switches (9750)
- Wireless (21)

Technology

- Capacitive (26)
- Electromechanical (9301)
- Microstructure (1486)
- NTC Thermistors (147)
- Thick Film (1764)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
 WGLA and WPMM
 XYR6000™

[find out more](#)

white papers

- ▶ Wireless Switches Offer Unlimited Benefit
- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters

Need help?

[Click here to contact us](#)


G Series Ceramic Automatic Reset stats

Actual product appearance may vary.

[Sales & Service](#)
[Distributor Inventory](#)
[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	0.5 A
Voltage	250 Vac/50 Vdc
Operating Temperature	0 °C to 260 °C [32 °F to 500 °F]
Environmental Exposure Range	-20 °C to 287 °C [0 °F to 550 °F]
Open Temperature	231.1 °C [448 °F]
Close Temperature	175.6 °C [348 °F]
Open Tolerance	10.0 °C [18 °F]
Close Tolerance	6.7 °C [12 °F]
Dielectric Strength	MIL-STD-202, Method 301; 2000 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm
Housing Material	Ceramic
Contact Material	WE -1 gold alloy cross point
Agency Approvals and Standards	UL, CSA, VDE
Mounting	B240 6-32 round cap stud
Series Name	3455RCG

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



- ▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login as Rep/AD
- ▶ Login as Guest
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING
- ▶ HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES
- ▶ HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

MICRO SWITCH
Anniversary site