

NUMBER


C-173981



METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST





注 ;

- 材料 : HSG - 66ナイロン樹脂UL94V-0
ポスト - 半田メッキ付黄銅
- 適用製品規格 : 108-5218
- 嵌合相手製品型番 : P/N 173977

NOTES;

- MATERIAL: HOUSING - 66 NYLON (UL94V-0)
POST - POST-PLATED TIN-LEAD BRASS
- PRODUCT SPEC., 108-5218
- APPLICABLE RECEPTACLE, P/N 173977

△ SUPERSEDED BY 292161

RECOMMENDABLE P.C. BOARD LAYOUT
推奨基板寸法(板厚 0.8-1.6)
(PCB THK: 0.8-1.6)

	△7-173981-5	△5-173981-5	△3-173981-5	△1-173981-5	15	28	31.8	25.2	31.0					
	△7-△	-4	△5-△	-4	△3-△	-4	1-△	-4	14	26	29.8	23.2	29.0	
	△7-	-3	△5-	-3	△3-	-3	△1-	-3	13	24	27.8	21.2	27.0	
△9-173981-2	△7-	-2	△5-	-2	△3-	-2	△1-	-2	12	22	25.8	19.2	25.0	
△9-△	-1	△7-	-1	△5-	-1	△3-	-1	1-	-1	11	20	23.8	17.2	23.0
△9-	-0	△7-	-0	△5-	-0	3-	-0	1-	-0	10	18	21.8	15.2	21.0
△8-	-9	△6-	-9	△4-	-9	△2-	-9		-9	9	16	19.8	13.2	19.0
△8-	-8	△6-	-8	△4-	-8	2-	-8	△	-8	8	14	17.8	11.2	17.0
△8-	-7	△6-	-7	△4-	-7	△2-	-7	△	-7	7	12	15.8	9.2	15.0
△8-	-6	△6-	-6	△4-	-6	△2-	-6	△	-6	6	10	13.8	7.2	13.0
△8-	-5	△6-	-5	△4-	-5	△2-	-5	△	-5	5	8	11.8	5.2	11.0
△8-	-4	△6-	-4	△4-	-4	2-	-4		-4	4	6	9.8	3.2	9.0
△8-▽	-3	△6-▽	-3	4-▽	-3	2-▽	-3	△▽	-3	3	4	7.8	—	7.0
△8-173981-2	△6-173981-2	△4-173981-2	2-173981-2	173981-2	2	2	5.8	—	5.0					
RED 赤色	BLACK 黒色	YELLOW 黄色	BLUE 青色	NATURAL 自然色	Pos. 極数	A	B	C	D					

WIRE RANGE	INSULATION DIA	NAME
—//— mm ² (AWG -)	—//— mmφ	ポストヘッダーアッセンブリ・垂直型 (V-タイプ) POST HEADER ASS'Y VERTICAL TYPE (AMP CT CONNECTOR 2mm PITCH)
MATERIAL SEE NOTE 1 注1参照	FINISH —//—	GENERAL TOLERANCE
DR. 4/5/90 T. NAKAMURA	DE. 10/27/95 T. NAKAMURA	SIZE LOC NUMBER B J C-173981
CHK. 4/5/90 S. KIKUCHI	APP. 10/27/95 S. KUBOUCHI	SCALE 5-1 REV. K2 SHEET 1 OF 1

CUSTOMER DRAWING