

[→ Honeywell.com](#) [→ Automation & Control Solutions](#)[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)[LOGIN](#)

Honeywell Sensing and Control

Search

**3001U 00240201**
Thermostats
(Home : Products)

narrow your search

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1705)
- Sensors (6325)
- Switches (9763)
- Wireless (4)

Technology

- Electromechanical (9306)
- Magnetic (541)
- Microstructure (1577)
- Optical/Infrared (1056)
- Thick Film (1764)
- More...

**3001 Series Non-Hermetic Thermostats**

Actual product appearance may vary.

[Sales & Service](#)[Distributor Inventory](#)

[contacts](#)

Customer Service
Technical Support
Global Sales & Service
View Site Demo
Site Comments?

[meet dr. larry](#)

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

Meet Dr. Larry



[my links](#)

[Login to iCOM](#)
[Login as Rep/AD](#)
[Login as Guest](#)
[Login to Digital University](#)

[News Center](#)

HONEYWELL EXPANDS
HAZARDOUS AREA LIMIT
SWITCH FAMILY TO FEATURE
A STAINLESS-STEEL SWITCH

HONEYWELL RELEASES
UNLIMITED POTENTIAL WITH
NEW LIMITLESS™ WIRELESS
SWITCHES

HONEYWELL'S XYR6000
WIRELESS POSITION SENSOR
ENABLES MONITORING IN
HAZARDOUS AREAS AND
REMOTE LOCATIONS

MICRO SWITCH
Anniversary site

[white papers](#)

[Basic Switches Are Not Created Equal](#)
[Applying Precision Switches](#)
[Sensors for Medical Devices](#)
[New Ways to Measure Torque](#)
[Choosing Safety Switches](#)
[Specifying Hour Meters](#)
[SAW Torque Sensor Technology](#)

[white papers](#)

[Basic Switches Are Not Created Equal](#)
[Applying Precision Switches](#)
[Sensors for Medical Devices](#)
[New Ways to Measure Torque](#)
[Choosing Safety Switches](#)
[Specifying Hour Meters](#)
[SAW Torque Sensor Technology](#)

[Need help?](#)

[Click here to contact us](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Functional Properties	Close on rise
Reset Type	Automatic
Amperage	3.0 A
Voltage	120 Vac
Operating Temperature	-18 °C to 168 °C [0 °F to 335 °F]
Environmental Exposure Range	-18 °C to 177 °C [0 °F to 350 °F]
Open Temperature	-12.2 °C [10 °F]
Close Temperature	-7.2 °C [19 °F]
Open Tolerance	2.2 °C [4 °F]
Close Tolerance	2.2 °C [4 °F]
Dielectric Strength	MIL-STD-202, Method 301; 1500 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm
Housing Material	Phenolic base with metal closure
Contact Material	Gold-plated silver
Agency Approvals and Standards	UL
Mounting	B209 fixed bracket
Series Name	3001

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)