
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	"X" INCH [mm]	"T" INCH [mm]	LENGTH INCH [mm]	WEIGHT LB/FT [Kg/m]
D2H6	1.79 [45.3]	.07 [1.7]	72.00 ±.13 [1829 ±3.3]	.096 [.143]
D3H6	2.74 [69.7]	.09 [2.21]		.165 [.245]
D4H6	3.53 [89.8]	.11 [2.8]		.285 [.426]
PANDUIT PART NUMBER	"X" MM [inch]	"T" MM [inch]	LENGTH MM [inch]	WEIGHT Kg/M [lb/ft]
D50H2	40.15 [1.6]	1.50 [.06]	2000 ±3.3 [78.74 ±.13]	.241 [.16]
D75H2	64.75 [2.5]	2.00 [.08]		.412 [.28]
D100H2	89.75 [3.5]	2.79 [.11]		1.45 [.97]

△H



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. THIS PART IS INTENDED TO BE USED WITH MOUNTING BASE DB-C IN ORDER TO SUCCEED AS A DIVIDER WALL APPLICATION.

△I △G

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
6	08-29-16	JBN	MRJS	RGRO	I. REMOVED DIM. "R" FROM CHART AND NOTE 3 H. ADDED METRIC DIVIDER WALL P/N: D50H2, D75H2, D100H2	34301-05
5	03-04-13	JBN	RTFI	RTFI	G. UPDATED DRAWING BORDER & TITLE BLOCK	34301-05

TITLE

SOLID DIVIDER WALL FOR WIRING DUCT AND FIBER DUCT (D2H6, D3H6, D4H6, D50H2, D75H2, D100H2)

CUSTOMER DRAWING

ITEM REVISION NAME: D34301BD/04

DATASET FILE NAME: D34301BD_DC_D2H6-D3H6-D4H6-D50H2-D75H2-D100H2

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ± .XXX ±

.XX ± ANGLES ±

THIRD ANGLE PROJECTION

MATERIAL: PVC

DRAWING NUMBER: 34301-05

DRAWN BY	DATE	CHK	SCALE	SIZE
DW	05-05-93	KRKE	NONE	A

SHT 1 OF 1

D10100DA/14

Downloaded from Arrow.com.