Part Number : 732306270
Product Description : SMA Straight Reverse Polarity Jack Bulkhead IP68 to I-PEX MHF4L LK Plug on 1.37mm Cable, 305.80mm Length, 50 Ohms
Series Number : 73230
Status : Active
Product Category : RF Cable Assemblies



Documents and Resources

Drawings

732306270_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF Cable Assemblies
Series	73230
Description	SMA Straight Reverse Polarity Jack Bulkhead IP68 to I-PEX MHF4L LK Plug on 1.37mm Cable, 305.80mm Length, 50 Ohms
Application	RF
Assembly Configuration	Dual Ended Connectors
Connector to Connector	SMA-to-I-PEX MHF
Product Name	I-PEX MHF,SMA
Type	RF Cable Assembly
UPC	196823189197

Electrical

Frequency	12 GHz
Impedance	50Ω

Physical

Cable Length	305.80mm
Gender	RP Jack/Plug
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	PTFE, Liquid Crystal Polymer
Net Weight	5.300/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	1.37mm Coaxial

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
SMA Plugs and Jacks	73391
SMA Plugs and Jacks	73251

Downloaded from Arrow.com.