



X
(without protection cap)



Loading-Plan

A black
B orange

-Temperature range: $-20^{\circ}\text{C} \dots +70^{\circ}\text{C}$
-Protection level: IP 20

For Information Only
-won't be replaced when changed-

Cont No.	Type of cable	Part-No.	Dim. a[mm]
5	Fiber optic cable, 8mm, POF	33 02 111 020 0001	20000
4	Fiber optic cable, 8mm, POF	33 02 111 010 0001	10000
3	Fiber optic cable, 8mm, POF	33 02 111 005 0001	5000
2	Fiber optic cable, 8mm, POF	33 02 111 002 0001	2000
1	Fiber optic cable, 8mm, POF	33 02 111 001 0001	1000

All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maßel/Free size tolerances	
Mod.	Dat.	Name		Dat.	Name	Maßstab/Scale	
DRS970A				Detail.	22.07.11	RO	FO cable assembly, 1xIP20-FO-SCRJ,POF
				Insp.	22.07.11	RA	
				Stand.			
HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP			HARTING			TB 33 02 111 xxx 0001	Blatt/ page
						Sub.	