







PRODUCT NUMBER	PITCH
V7xx72x000J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



Material:

- Item ① Terminal housing: Thermoplastic (UL94V-0)
- Item ② Female contact: PhBz(CuSn), Tin plated
- Item ③ Terminal cover: Thermoplastic (UL94V-0)
- Item ④ Flange Nut: Brass M2.5

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:

N=Number of poles
Dim L=N×5.0+10.0
Dim A=N×5.0
Dim B=(N-1)×5.0
Dim C=(N-1)×5.0
Dim D=(N-1)×5.0+10.4

poles	Dim L	Dim A	Dim B	Dim C	Dim D
2-6p	±0.15	0	±0.15	±0.15	±0.15
7-12p	±0.20	-0.20	±0.20	±0.20	±0.20
13-18p	±0.30	0	±0.30	±0.30	±0.30
19-24p	±0.40	-0.30	±0.40	±0.40	±0.40

PART NO.: V7 xx 7 2 x 0 00J0 G

Solid block
No. of poles
02 2poles
03 3poles
...
24 24poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK													
ltr	ecn	no	dr	date		tolerances unless otherwise specified						title TERMINAL BLOCK											
						line 0.1		X.±0.5		MM		PLUGGABLE PCB PLUG,WITH FLANGE,VERTICAL											
					X.X±0.3																		
					X*±1°																		
						dr		EVIN ZHONG		043014		dwg no				sheet 1 of 1		size					
						enrg		EVIN ZHONG		043014		V7xx72x000J0G				A4							
						chr		HANKE FENG		043014													
						appd		SHI JUN		043014		FCI 				type				CUSTOMER Drawing			
sheet index		revision		A																			
		sheet		1																			