

4


3

2

1

used for:

D-SUB



(b)

No. of pos.	A	B	C	D	E	ØF	Part-N0.
9	31.8	25.0	39.5	42.0	17.6	10.6	165X04679A
15	41.3	33.3	45.5	48.0	16.3	11.5	165X04689A
25	54.9	47.0	52.5	55.2	16.3	12.0	165X04709A
37	71.8	65.5	55.5	58.2	18.7	14.5	
50	69.0	61.1	55.0	57.8	19.5	15.0	

(d)

Directive 2002/95/EC
"RoHS"
Compliant

TECHNICAL DATA:

MATERIAL: PBT UL 94 V-0

COLOUR: BLACK

TEMPERATURE RANGE: -33°C to + 90°C

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		
1 x d	Ä 2382	17.11.2005	Lehmen	2005	date	
1 x c	Ä 2374	07.11.2005	Lehmen	drawn	25.10.	name
2 x b	Ä 2362	26.10.2005	Lehmen	appd.	25.10.	Mickenbecker
rev.	description	date	name	norm		

scale:	1:1
material:	SEE TECHNICAL DATA
title:	PLASTIC HOOD 9-50pos. with straight cable exit
dwg no:	AutoCAD 2004
part no:	SEE TABLE

PLASTIC HOOD

9-50pos.

with straight cable exit

16K1A1533

DIN-A

4

sh: 1/1

4

3

2

1