

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Female Plugs

General Information

Extended Product Type:	F.MF16/4
Product ID:	1SNA113208R0200
EAN:	3472591132083
Catalog Description:	F.MF16/4 Female Plugs Grey
Long Description:	Each contact is numbered on the two elements of the housing.

Ordering

Color:	Grey
Minimum Order Quantity:	10 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Weight:	3 g
----------------------------	-----

Technical

Function:	Female Plugs
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 ... 1.5 mm ² Screw Clamp / Rigid 1x 0.22 ... 1.5 mm ²
Rated Voltage (U_r):	750 V
Pollution Degree:	3
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Certificates and Declarations (Document Number)

CSA Certificate:	1SND164002A0200
Declaration of Conformity - CE:	1SSD235034C1001

Classifications

Object Classification Code:	X
ETIM 4:	EC002638 - Cable connector
ETIM 5:	EC002638 - Cable connector
ETIM 6:	EC002638 - Cable connector

Container Information

Package Level 1 Units:	10 piece
-------------------------------	----------

Package Level 1 Gross Weight:	0.03 kg
Package Level 1 EAN:	3472591132083
Package Level 2 Units:	1000 piece

