

Power Extension Cord, NEMA 5-15P to NEMA 5-15R - Heavy-Duty, 15A, 120V, 14 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: **P024-010**



10 ft. extension cord connects your computer or other device with a NEMA 5-15P plug to a PDU or UPS with a NEMA 5-15R outlet.

Features

Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection This 10-ft. (3.05 m) extension cord features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, monitor, printer or other device with a NEMA 5-15P plug to a wall outlet, PDU, surge protector or UPS system with a NEMA 5-15R outlet. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Specifications

| OVERVIEW | |
|-----------------------------|---|
| UPC Code | 037332180612 |
| Device Compatibility | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 15 |
| Voltage Compatibility (VAC) | 125 |
| PHYSICAL | |
| Plug Color | Black |
| Cable Jacket Color | Black |

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing 10-ft. (3.05 m) extension cord

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P024-010 10-ft. (3.05 m) Extension Cord, NEMA 5-15P to NEMA 5-15R, Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--------------------------------------|-------------------------------|
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 9.3mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 14 |
| Wire Gauge (OD - mm ²) | 2.08 |
| Cable Length (ft.) | 10 |
| Cable Length (m) | 3.05 |
| Shipping Dimensions (hwd / cm) | 2.54 x 17.78 x 27.94 |
| Shipping Dimensions (hwd / in.) | 1.00 x 7.00 x 11.00 |
| Shipping Weight (kg) | 0.50 |
| Shipping Weight (lbs.) | 1.10 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4 F TO 140 F (-20 C TO 60 C) |
| Storage Temperature Range | -4 F TO 140 F (-20 C TO 60 C) |
| Operating Humidity Range | 10 TO 65% RH |
| Storage Humidity Range | 10 TO 65% RH |
| CONNECTIONS | |
| Side A - Connector 1 | NEMA 5-15P |
| Side B - Connector 1 | NEMA 5-15R |
| FEATURES & SPECIFICATIONS | |
| High Voltage | No |
| Locking Plug | No |
| Angled Plug | No |
| STANDARDS & COMPLIANCE | |
| Certifications | UL/cUL |
| Approvals | UL/CSA |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>