




X (2:1)





Loading-Plan
(Data)




Loading-Plan
(Power-DC version)



Y (2:1)



		All Dimensions in mm Original Size DIN A3		Scale 1:1		Free size tol.		Ref.		
								Sub.		
		All rights reserved		Created by POPESCUD		Inspected by AVRAM		Standardisation HOFFMANN		
		Department EC PD - RO				Date 2015-12-18		State Final Release		
HARTING Electronics GmbH D-32339 Espelkamp		Title Han 3A RJ45 Hybrid Cable Assembly							Doc-Key / ECM-Nr. 100154019/UGD/013/C 500000098235	
		Type TB		Number 33572110XX000X					Rev. C	
									Page 1/2	



7	33572110200002	Hybrid cable 4x2AWG26/7+3x2.5 sqmm, 2xHan 3A, DC	20
6	33572110100002		10
5	33572110060002		6
4	33572110050002		5
3	33572110030002		3
2	33572110020002		2
1	33572110010002		1
Cont. no.	Part-no.	Type of cable	Dim. a[m]

		All Dimensions in mm		Scale 1:1		Free size tol.		Ref.					
		Original Size DIN A3						Sub.					
		All rights reserved		Created by POPESCUD		Inspected by AVRAM		Standardisation HOFFMANN		Date 2015-12-18		State Final Release	
		Department EC PD - RO											
HARTING Electronics GmbH D-32339 Espelkamp		Title Han 3A RJ45 Hybrid Cable Assembly								Doc-Key / ECM-Nr. 100154019/UGD/013/C 500000098235			
		Type TB		Number 33572110XX000X						Rev. C		Page 2/2	