

## Description

- Industry standard leaded package  
Resistance welded, hermetically sealed in an inert atmosphere, glass to metal seals on leads
- Standard 2 leg HC49 package
- Model HC49
- Model Issue number 15

## Frequency Parameters

- Frequency 33.330MHz
- Frequency Tolerance  $\pm 30.00\text{ppm}$
- Frequency Stability  $\pm 50.00\text{ppm}$
- Operating Temperature Range  $-20.00$  to  $70.00^{\circ}\text{C}$
- Overtone Order 3RD
- Ageing  $\pm 3\text{ppm}$  typical per year

## Electrical Parameters

- Load Capacitance 10.00pF
- Shunt Capacitance 7pF max
- Drive Level 1mW max
- ESR 40.00 $\Omega$  max

## Environmental Parameters


- Shock: 981m/s<sup>2</sup>, 6ms, 3 times in each of 3 mutually perpendicular planes
- Vibration: 10Hz-60Hz, 0.75mm amplitude, 60Hz-500Hz, 98.1m/s<sup>2</sup>, 30mins in 3 mutually perpendicular planes
- Storage Temperature Range:  $-55$  to  $125^{\circ}\text{C}$

## Compliance


- RoHS Status (2011/65/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

## Packaging Details

- Pack Style: Bulk Loose in bulk pack  
Pack Size: 100
- Alternative packing option available



## Outline (mm)



## Sales Office Contact Details:

UK: +44 (0)1460 270200  
Germany: 0800 1808 443

France: 0800 901 383  
USA: +1.760.318.2824

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)  
Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)