

# ME MAX B-17,5 KMGY - Filler plug



2706959

<https://www.phoenixcontact.com/us/products/2706959>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug for unoccupied terminal points, width: 15 mm, height: 21.6 mm, depth: 8.1 mm, color: light gray (similar RAL 7035)

## Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

Item number	2706959
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AC08
Product key	ACHABZ
Catalog page	Page 685 (C-1-2013)
GTIN	4017918925260
Weight per piece (including packing)	0.848 g
Weight per piece (excluding packing)	0.827 g
Customs tariff number	39269097
Country of origin	DE

# ME MAX B-17,5 KMGY - Filler plug



2706959

<https://www.phoenixcontact.com/us/products/2706959>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX 17,5..
Type	Filler plug for unoccupied terminal points
Ventilation openings present	no

### Dimensions

Width	15 mm
Height	21.6 mm
Depth	8.1 mm

### Material specifications

Color (Housing)	light gray (RAL 7035)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	Latching
---------------	----------

### Packaging specifications

Outer packaging type	Resealable bag
----------------------	----------------

# ME MAX B-17,5 KMGY - Filler plug

2706959

<https://www.phoenixcontact.com/us/products/2706959>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2706959>



**UL Recognized**

Approval ID: E240868

# ME MAX B-17,5 KMGY - Filler plug



2706959

<https://www.phoenixcontact.com/us/products/2706959>

## Classifications

### ECLASS

ECLASS-13.0	27190605
-------------	----------

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME MAX B-17,5 KMGY - Filler plug



2706959

<https://www.phoenixcontact.com/us/products/2706959>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)