



Part Number : 936010559
Product Description : Heavy-Duty Crimp Contact Insert, Male, 17-Pole, 10A, for Turned Crimp Contacts, Size «34.2x14.6»
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 7717.3426.0



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Crimp Contact Insert, Male, 17-Pole, 10A, for Turned Crimp Contacts, Size «34.2x14.6»
Component Type	Inserts - Crimp Contact
Insert Series	S-M10/17
Product Name	Heavy-Duty Connectors
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191834863

Agency

UL	E249674
----	---------

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	160V

Physical

Component Size	«34.2x14.6»
Durability (mating cycles max)	500
Gender	Male
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	8.400/g
Number of Rows	3
Packaging Type	Bag
Polarized to Mating Part	Yes

Poles	17
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Heavy-Duty Crimp Contact Insert, Female, 17-Pole, 10A, for Turned Crimp Contacts, Size «34.2x14.6»	<u>936010558</u>

Use with Part(s)

Description	Part Number
Use With	Turned Crimp Contacts - Male

This document was generated on Sep 23, 2025