



Part Number : [1301020202](#)
Product Description : Super-Safeway Rubber Hand Lamp with 300W, Open End Vinyl Coated Guard with Reflector, with Switch and Receptacle, 7.62m (25.0') 16/3 SOOW
Series Number : 130102
Status : Obsolete
Product Category : Lamps and Lights
Engineering Number : 115USIA163



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Lamps and Lights
Series	130102
Description	Super-Safeway Rubber Hand Lamp with 300W, Open End Vinyl Coated Guard with Reflector, with Switch and Receptacle, 7.62m (25.0') 16/3 SOOW
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678860517

Electrical

Lamp Wattage - Maximum	300W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	190.50mm (7.500")
Duty	Industrial
Guard Included	Yes
Guard Type	Insulated, Open End, Reflector
Height	371.35mm (14.620")
Lamp Type	A23
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	Side
Packaging Type	Carton

This document was generated on Apr 26, 2025