Data sheet

ESO 7 DIN A4 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Terminal markers, Insert markers, 27 x 6.3 mm, yellow
Order No.	1634780000
Type	ESO 7 DIN A4 GE
GTIN (EAN)	4008190273361
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Available until	2026-01-30T00:00:00+01:00
Alternative product	THM ESO 7 PA GE

Downloaded from Arrow.com.

Data sheet

ESO 7 DIN A4 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	27 mm	Height (inches)	1.063 inch
Width	6.3 mm	Width (inches)	0.248 inch
Net weight	9.15 g		

Temperatures

Operating temperature range	-40...80 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4	
Orientation of print	horizontal and vertical	
Number per sheet	240	
Width	6.3 mm	
UL 94 flammability rating	HB	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Colour	yellow	
Basic material	Paper	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label sheet
Number of markers per combination	1 Label sheet = Insert markers	
Operating temperature range	-40...80 °C	

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Downloaded from Arrow.com.

ESO 7 DIN A4 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

WKM for inlay tags



The halogen-free, transparent pocket of the WKM offers outstanding protection against environmental influences. Thanks to firm fixation with cable ties, it is suitable for almost all wire cross-sections.
The pre-printed tags are simply inserted into the WKM holder and secured with a clip. WKM cable markers are the right solution for maximum efficiency in on-site marking. Your advantage when using WKM cables

- Paper and polyester labels can be printed individually with conventional office printers
- The robust design in combination with MultiCard ELS tags guarantees maximum protection against environmental influences

General ordering data

Type	WKM 8/30	Version
Order No.	1631910000	WKM, Conductor and cable markers, 7 - 115 mm, 30 x 8 mm, Wire
GTIN (EAN)	4008190206666	and cable markers, Transparent
Qty.	50 ST	

Downloaded from Arrow.com.