






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REVISED PER ECN-22-144478	19MAY2022	AK	SZ




REFERENCE P.C.B LAYOUT
(SIDE VIEW,1.3mm THK)







- ① MATERIAL
HOUSING: THERMO-PLASTICS,UL94V-0
CONTACT: COPPER ALLOY
FRONT SHELL: COPPER ALLOY
BACK SHELL: COPPER ALLOY
- ② FINISH
CONTACT: NICKEL UNDER PLATE ALL OVER.
CONTACT AREA: GOLD PLATING
TINE AREA: Tin PLATING
FRONT SHELL: Tin PLATING,Ni UNDER PLATING
BACK SHELL: Ni PLATING
- ③  NO COMPONENT AREA.


OBSOLETE	CERAMICS WHITE	1746311-2
	BLACK	1746311-1
	COLOR	PARTS No.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.CHIEN		15MAR04		 TE Connectivity Ltd.	
		CHK T.FUTATSUGI		15MAR04			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD H.KODAMA		NAME	
		0 PLC ±		PRODUCT SPEC		USB CONNECTOR RECEPTACLE DIP AND OFFSET TYPE	
		1 PLC ±		108-5983			
		2 PLC ± 0.3		APPLICATION SPEC		SIZE	
		3 PLC ±				CAGE CODE	
		4 PLC ±				DRAWING NO	
		ANGLES ± 3°		RESTRICTED			
MATERIAL		FINISH		WEIGHT		A3 00779 C-1746311	
				CUSTOMER DRAWING		SCALE 4:1	
						SHEET 1 of 2	
						REV H	







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



INNER LABEL



TRAY WITH TOP COVER



- NOTES :
- MATERIAL:
TRAY : PS , T=0.8~1.0
SHIPPING CARTON : CORRUGATED FIBERBOARD
 - DIMENSION
TRAY : L=300, W=215, H=10
SHIPPING CARTON : L=320, W=230, H=200
 - QUANTITY:
63 PCS/TRAY
819 PCS/SHIPPING CARTON
 - WEIGHT:
NET WEIGHT:1.24KG
GROSS WEIGHT:2.53KG

USB CONNECTOR PACKING METHOD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity Ltd.		
		CHK			
		APVD	NAME		
		PRODUCT SPEC	USB CONNECTOR RECEPTACLE DIP AND OFFSET TYPE		
		APPLICATION SPEC			
		WEIGHT	SIZE	CAGE CODE	DRAWING NO
			A3	00779	C-1746311
		CUSTOMER DRAWING	SCALE	SHEET	REV
				2 OF 2	H