

Product data sheet

Specifications



APC IT Power Distribution Module 3 Pole 5 Wire 16A IEC309 200cm

PDM3516IEC-200

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

General

Provided equipment	Installation guide
--------------------	--------------------

Physical

Colour	Grey
Depth	40.6 cm
Height	15.2 cm
Net weight	1.59 kg
Width	43.2 cm

Input

Network frequency	50 Hz
Max line current	16 A
Input voltage	400 V 3 phases

Output

Max current draw	16 A
Number of power socket outlets	1 IEC 309 16 A
Output voltage	230 V 400 V 3 phases

Conformance

Product certifications	CE VDE
------------------------	-----------

Packing Units

Package 1 Weight	2.5 kg
Package 1 Height	15.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 width	43.2 cm
Package 1 Length	40.6 cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------