molex

**Part Number :** 191640057
**Product Description :** Perma-Seal Butt Splice for 12-10 AWG Wire, Mylar Tape Carrier
**Series Number :** 19164
**Status :** Active
**Product Category :** Splices
**Engineering Part Number :** SC-12-10T



## Documents and Resources

### Drawings

191640057_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-19902-015-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Splices |
| Series | 19164 |
| Description | Perma-Seal Butt Splice for 12-10 AWG Wire, Mylar Tape Carrier |
| Product Name | Perma-Seal |
| Style | Standard |
| Type | Butt Splice |
| UPC | 800753113428 |

### Agency

| | |
|---|---|
| CSA | LR18689 |
| UL | E32244 |

### Electrical

| | |
|---|---|
| Voltage - Maximum | 600V |

### Physical

| | |
|---|---|
| Barrel Type | Closed |
| Color - Resin | Yellow |
| Insulation | NiAc |
| Material - Metal | Copper |
| Material - Plating Mating | Tin |

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Plating Termination | Tin |
| Net Weight | 3.422/g |
| Packaging Type | Adhesive Tape on Reel |
| Temperature Range - Operating | -55° to +125°C |
| Wire Insulation Diameter | 7.87mm max. |
| Wire Size (AWG) | 10, 12 |

## Application Tooling

### Global

| Description | Part Number |
|---|---|
| ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press | 192880279 |
| PremiumGrade Hand Crimp Tool for Industrial Terminals, 22-10 AWG (see ATS) | 640017400 |
| Power Crimp Tool Head for Terminals 22-10 AWG Wire | 640057400 |
| ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool | 640160041 |



Downloaded from Arrow.com.