Representative Image

Catalog No. TC826-TB

Description: 2WAY MNTG BASE .96X.5IN NAT NYL SCR

UPC No 5414363075066

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Cross-Fastening Screw-Mounted Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 24.31mm (0.957 Inches), Width of 13.21mm (0.52 Inches), Height of 5.97mm (0.235 Inches), Screw Mounting Method, #8 Screw, Mounting Hole Diameter of 4.4mm (0.173 Inches)

Descriptors

Category	Cable tie mounts
Special Features	These mounting bases can be used to tie bundles running parallel or perpendicular to length of base.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap

Dimensions

Mount Size	#8

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	24.31 mm
Length	0.96 inch
Width	13.21 mm
Width	0.52 inch
Height	5.97 mm
Height	0.24 inch

by ABB

Downloaded from Arrow.com.

ETIM	EC000449 Mounting base and -element for cable ties
Type of fastening	Other
Diameter mounting hole	4.4 mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E16592	N/A	FKAV	N/A	N/A

Downloaded from Arrow.com.