Part Number : 1200710087
Product Description : Micro-Change (M12) Field Attachable Connector, 4 Poles, Straight, Female, Unshielded, IDC Termination, Cable Diameter 3.50-6.00mm
Series Number : 120071
Status : Active
Product Category : Circular Industrial Connectors
Engineering Part Number : 8A4000-51

Documents and Resources

Drawings

1200710087_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120071
Description	Micro-Change (M12) Field Attachable Connector, 4 Poles, Straight, Female, Unshielded, IDC Termination, Cable Diameter 3.50-6.00mm
Approvals	cRUus - UL Recognized
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Field Attachable Connector
UPC	889056509527

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	125V

Physical

Cable Diameter	3.50-6.00mm (.138-.236")
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Single
Material - Connector Body	PA
Material - Contact	Copper Alloy

Downloaded from Arrow.com.

Material - Coupling Nut	Zinc Die-Cast, Nickel-Plated
Material - Plating Mating	Gold
Net Weight	18.000/g
Orientation	Straight
Poles	4
Temperature Range - Operating	-25° to +80°C
Wire Size (AWG)	22-26

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Change (M12) Field Attachable Connector, 4 Poles, Straight, Male, Unshielded, IDC Termination, Cable Diameter 3.50-6.00mm	1200710086

Downloaded from Arrow.com.