

85891 - 3 Product Details

Live Product Chat

US Only

8:30am - 5pm ET, Mon - Fri



85891 - 3

Active

Contacts - AMPMODU Machine Applied

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ?

 Contact Type = Square Post
- ?

 Length = 21.03 mm
- ?

 Phosphor Bronze Contact Material
- ?

 Gold (15) over Nickel Contact Mating Area Plating Material
- ?

 Loose Piece

[View all Features](#) | [Find Similar Products](#)

Quick Links

[Check Pricing & Availability](#)

[Search for Tooling](#)

[Product Feature Selector](#)

[Contact Us About This Product](#)

Documentation & Additional Information	
Product Drawings: ? None Available Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? AMPMODU Mod I And II Posts (PDF, English) Instruction Sheets: ? None Available CAD Files: ? None Available	Additional Information: ? Product Line Information Related Products: ? Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? With Insulation Support = Yes Termination Related Features: ? Solder Tail Contact Plating = Gold over Nickel Body Related Features: ? Length (mm [in]) = 21.03 [0.828] Contact Related Features: ? Contact Type = Square Post ? Contact Material = Phosphor Bronze ? Contact Mating Area Plating Material = Gold (15) over Nickel	Industry Standards: ? RoHS/ELV Compliance = RoHS compliant, ELV compliant ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C ? RoHS/ELV Compliance History = Always was RoHS compliant Packaging Related Features: ? Packaging Method = Loose Piece Other: ? Brand = AMP