

Specifications



Photo is representative

Eaton C22-WRK-K10-P32

Eaton, 22.5 mm RQM Compact Pushbutton, 2 position knob, Silver bezel, 1.0 m M8, 4-pole wire, 1NO, IP65, Non-Illuminated, Flush mounting, NEMA 4X, 13,1,000,000 operations, Maintained, 22.5 mm, Flush Pushbutton, C22 Series

General specifications

PRODUCT NAME	Eaton C22 compact pushbutton
CATALOG NUMBER	C22-WRK-K10-P32
EAN	4015081816521
PRODUCT LENGTH/DEPTH	42.36 in
PRODUCT HEIGHT	1.18 in
PRODUCT WIDTH	1.18 in
PRODUCT WEIGHT	0.119453 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DIN VDE 0600
CERTIFICATIONS	EN 60947 IEC 60947 CSA Certified UL Listed

Product specifications

TYPE	Compact pushbutton
BEZEL	Silver
ACTUATOR FUNCTION	Maintained
ENCLOSURE	IP65
ACTUATOR	2 position knob
OPERATING MODE	Maintained
CONTACT CONFIGURATION	1 NO
ILLUMINATION	Non-illuminated
SERIES	C22
OPERATING CYCLES	1 million
MOUNTING METHOD	Flush
DEGREE OF PROTECTION	NEMA 4X NEMA 13
PRODUCT CATEGORY	Flush pushbutton
SIZE	22.5 mm

Resources

MULTIMEDIA	How to size and select a Power Supply
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C22-WRK-K10-P32

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

