



BDBMHC222/01

by Burndy
Catalog ID: BDBMHC222/01

Prop 65 Notice

POWER DISTRIBUTION BLOCKS.

Single or dual run connections allow the user to minimize the number of connections required, Adders and End Barriers available separately for all 3 sizes providing capability to create as many poles as required

Product Details

General

| | |
|--------------------|---|
| Application | Suitable for use with aluminum or copper conductors providing maximum versatility |
| Insulation | Y |
| Material | Aluminum |
| Number Of Poles | 1 |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | VERSIPOLE |
| Temperature Rating | 194 |
| Trade Name | VERSIPOLE™ |
| Type | BDBMH |
| UPC | 781810645901 |
| UPC 12 Digit | 7818106459011 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 3.25 in |
| Dimension - L Length Overall mm | 127 mm |
| Dimension - Length Overall inch | 5.00 in |
| Dimension - Width inch | 1.85 in |
| Dimension - Width mm | 47 mm |

Electrical Ratings

| | |
|--------------------------|-------|
| Amperage Rating | 350 A |
| Rating - Minimum Voltage | 600 |

Conductor Related

| | |
|----------------------------------|------------------------------------|
| Conductor - AL Str Run | 12;10;8;6;4;3;2;1;1/0;2/0 |
| Conductor - AL Str Run Range | 12-2/0 |
| Conductor - AL Str Tap | 12;10;8;6;4;3;2;1;1/0;2/0 |
| Conductor - AL Str Tap Range | 12-2/0 |
| Conductor - Copper Str Run | 14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0 |
| Conductor - Copper Str Run Range | 14-2/0 |

| | |
|----------------------------------|---|
| Conductor - Copper Str Tap | 14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0 |
| Conductor - Copper Str Tap Range | 14-2/0 |
| Conductor Type | <ul style="list-style-type: none">• AL C Str-Run• CU C Str-Run• AL C Str-Tap• CU C Str-Tap |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 18 EA |
| Minimum Pack Quantity | 1 |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)