9-1377172-4 Product Details



9-1377172-4

TE Internal Number: 9-1377172-4

Active

Ring and Spade Tongue Terminals

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Body Style = PLASTI-GRIP
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- SMALL PACK (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Receptacle Style = Straight
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire
- Insulation = Yes
- Insulation Support = Insulation Support
- Stud Size = 6 [M3.5]
- Shape = RING-043
- Heavy Duty = No
- Finish = Tin

Termination Features:
- Wire/Cable Size (CMA) = 509 - 3,260

Dimensions:
- Insulation Diameter (mm [in]) = 3.56 [.140] Max.
- Stud Diameter (mm [in]) = 3.68 [0.145]

Body Features:
- Body Style = PLASTI-GRIP
- Wire Range (mm [AWG]) = 0.30-1.42² [22-16]
- Material = Copper

Contact Features:
- Terminal Shape = Ring Tongue

Industry Standards:
- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Features:
- Packaging Method = Loose Piece
- Packaging Quantity = 100

Other:
- Brand = AMP

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

Downloaded from Arrow.com.