



Catalog No. 147

Description: 2-1/2INCH LOCKNUT

UPC No 786210001470

Home > Cable Protection Systems > T&B Liquidtight Fittings > Locknuts

2-1/2 Inch Malleable Iron Locknut for Use With Rigid/IMC Conduit

Descriptors

Category	Locknuts
Special Features	Hardened Steel, Malleable Iron, Copper-Free Aluminum Construction
Application	To Connect Externally Threaded Conduit or Connector to a Threadless Opening In a Box or Enclosure.

Specifications

Material of Construction	Malleable Iron
--------------------------	----------------

Classifications

Brand Name	T&B Liquidtight Fittings
Standard	UL E23018, CSA

Dimensions

Thread Size	2-1/2 in
-------------	----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC002382 Locknut
Material	Other
Surface protection	Untreated
With nylon ring	N
Height	90.42 mm
Height	3.56 inch

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	2884	441202	N/A	N/A	N/A
UL	E23018	N/A	DWTT	N/A	N/A