

2TP216-1-L1

[Products](#) > [Switches](#) > [Rocker Switches](#) > [TP Series](#) > **2TP216-1-L1**

Overview

TP Series Rocker Switch, 2 pole, 3 position, Screw terminal, Above Panel Mounting.
MICRO SWITCH TP Rocker switches may be mounted flush or above panel.
[View More](#)



view all 2TP216-1-L1 literature

view distributor inventory

sample request

email support

get support

email sales

find a distributor

email this page

Technical Specifications

Circuitry	DPDT	Action	3 position
Circuitry/Operating action		Mounting	Above Panel
Lamp Type	Translucent	Termination	Screw
Ampere/Voltage Range (Resistive Load)	0.75 A at 115 Vdc 0.5 A at 250 Vdc 0.5 A to 20 A at 0.5 Vdc to 28 Vdc 0.5 A to 15 A at 0.5 Vac to 277 Vac	Contact Type	Silver Cadmium Oxide Contacts
Product Type	MICRO SWITCH Rocker	LED/Lamp/Neon Voltage	L191: 15 A-125, 250, 277 Vac; 1/2 Hp-125 Vac; 1 Hp-250, 277 Vac; 5 A-120 Vac "L"

[View More](#)

View documents in:

English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
2TP216-1-L1 highres photo	Photo	--	1MB
2TP216-1-L1 lowres photo	Photo	--	145KB
MICRO SWITCH TP Series Rocker Switches Datasheet	Datasheet	English	1MB
TP Series Rocker Button Switches	Catalog Information	English	391KB

[View More](#)

Product Features

- Environmentally sealed
- Two and three-position pushbutton action
- Various button colors
- 1, 2, and 4-pole circuitry
- Flush panel and above panel mountings
- Temperature range: -54 °C to +71 °C [-65 °F to +160 °F]

- UL recognized, CSA certified
- CE approved

Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Marine applications
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.